


# PRODUCT SPECIFICATION

<b>Brand</b>	C.K
<b>Product Range</b>	Fast4

<b>Range Description</b> 4 flute wood drill bits	
<b>Features</b> <ul style="list-style-type: none"> <li>• 4 flute configuration for fast waste removal</li> <li>• 100% more cutting blade than a flat bit or auger</li> <li>• Side blade for clean breakout</li> <li>• Nose screw pulls the bit through – less effort</li> <li>• Clean hole profile</li> <li>• Class leading cutting speeds</li> <li>• 2943 - Fast change docking system (to 25mm)</li> <li>• 2944 – SDS Plus docking system on all sizes</li> </ul>	

Item Number	Item Description
TL12833	Fast4 wood drill bit 16mm
TL12834	Fast4 wood drill bit 20mm
TL12835	Fast4 wood drill bit 22mm
TL12836	Fast4 wood drill bit 25mm
TL12837	Fast4 wood drill bit 32mm

Technical product information	Recommended cutting speeds: 16 – 20mm between 1500 - 2000 RPM 22 – 25mm between 1000 – 1500 RPM 32mm            between 800 – 1300 RPM  2943 - Fast change docking system (6.4mm) hex shank provided on sizes up to 25mm Size 32mm has an 11mm hex drive shaft
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations

Material safety data	None applicable
Warranty	C.K products are guaranteed for life against imperfect materials or workmanship Normal wear and tear of cutting edges and damage caused through inappropriate use is not covered
Country of origin	Taiwan