



The **tec305** lightweight, professional glue gun offers unrivalled reliability, ease of use and exceptional adhesive melt rate for a glue gun of this size. High quality, self-regulating heaters control the glue gun temperature and is designed to provide years of trouble free service. Suitable for schools, colleges and out-workers where a safe, reliable glue gun is essential. Ideally suited to applications where small quantities of adhesive are required repetitively in product assembly, packaging, and general use.

- > Comfortable and easy to use.
- > Reaches full operating temperature in just 5 minutes.
- > Glue output of over 750 grams (1½lbs) per hour.
- > Narrow profile aids visibility, allowing molten glue to be placed with high accuracy.
- > Runs on most voltages from 110V to 240V.
- > Fitted with eco efficient self regulating 20W (150W) heaters.
- > Adjustable full-hand lever trigger for optimum comfort and metered shots.
- > Multifunctional detachable base stand includes a nozzle wrench.
- > Illuminated ON/OFF switch.
- > Weighs only 230g (8oz).
- > Designed to use standard 12mm (½") **tecbond** high performance hotmelt glue sticks.
- > The **tec 305** is built to comply with worldwide industrial and electrical safety standards and is covered by a full one-year warranty.



12mm (½")
extension nozzle
& rubber shroud



Takes 12mm (½")
glue sticks



Detachable stand
with nozzle wrench



Narrow profile to aid
visibility



Illuminated
ON-OFF switch



Comfortable to use
with adjustable
full-hand trigger

Power adhesives Tec 305 Glue Gun options:

TEC305-12-UK : HOTMELT 190° with UK Mains plug.

TEC305LT-12-UK: LOWMELT 130° with UK Mains plug

TEC305-12-UK -KIT: HOTMELT 190° with UK Mains plug.

Kit content:

20 x Clear TECBOND 232-12-200, 1 x TEC MAT supplied in a plastic case.

TEC305-12-EU : HOTMELT 190° with EURO Mains plug.

TEC305LT-12-EU: LOWMELT 130° with EURO Mains plug