


## **Products**

## Neon & Incandescent Indicators

CML IT offers panel mount indicators manufactured with LED, Neon or Incandescent light sources. These indicators are available in a number of different lens and termination styles, with voltages of 2V ~ 250V available off-the-shelf.



Part Number: 2390QD1-28V Serial Number: 2390 Light Source: Incandescent Color: Red

Voltage (V): 28V

Mounting Hole (inch): 1.276 x .395

Mounting Hole (metric): 32.41 x 10.03


Termination: .250" QC

Bezel color: Stainless Steel Housing color: White **UL file:** E20325 CSA file: LR13346 RoHS Status: Yes



## 2330QD, 2332QD and 2390QD Series Non-Relampable Neon-Incandescent Indicator Lights

## DESCRIPTION AND FEATURES



Mounting: Will snap-fit into .032/.100 thick panel, use speednut for other panel thicknesses. Available with speednut SN1963.

Mounting hole pattern on page SP3.

Terminals: Quick-connect, tinned brass.

Lens: Polycarbonate

Bezel: Polished stainless steel. For black finish add "X" after the series letter(s).

	Neon	Incandescent
Lens Color	Model No.	Model No.
	(105-125VAC)	(28V)
	.250 Terminals	.250 Terminals
Red	2330Q D1	2390Q D1-28V
Amber	2330Q D3	2390Q D3-28V
White	2330Q D4	2390Q D4-28V
Green	2332Q D5*	2390Q D5-28V
Lamp used	C6A+Resistor	#2187

\*Incorporates G2B lamp and resistor Underwriters Laboratories (UL) File No. E20325 Canadian Standards Association (CSA) File No. LR13346

