

EK EKOE 130 G



Sample photo

Order symbol:	EKOE 130 G
Product nbr:	2538037
Description:	Enclosure, PC
Remarks:	Grey cover

EAN:	6418074013569
El. number:	
Finland:	3425418
Italy:	7501040
Sweden:	2538037
Norway:	

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height
mm:	280	280	130
inch:	11.0	11.0	5.1

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035
Cover colour:	RAL 7035
Cover screws material:	Polyamide
Cover screws colour:	Grey
Gasket material:	Polyurethane

Temperatures:

Short term:	-40 ... 120 °C
Continuous:	-40 ... 80 °C
Short term:	-40 ... 250 °F
Continuous:	-40 ... 175 °F

Accessories:

EKO E	Base, PC
EKO 30-G	Cover
EKO 80-G	Cover
EKO 30-T	Cover
EKO 80-T	Cover
EKOVT	Mounting plate
EKOXT	Mounting plate Pertinax
EKV 22	DIN-35 Mounting rail
EKOZR	Extension frame

Rating:

Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 62262): IK 08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
UV resistance: UL 508
Flammability Rating (UL 746 C 5): UL 746C 5V
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Certificates:

- Germanischer Lloyd (GL)
- Underwriters Laboratories
- Det Norske Veritas
- Bureau Veritas
- Fimko
- Lloyds Register of Shipping (LR)
- Europe EN 62208: 2003
- UL Canada
- Gost R

EK 280x280x130-180

