



**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™

BIT,STEP #1 (PKGD).

Kwik Stepper® Step Bits



Image  
Unavailable

Cat No: 34401

UPC No: 783310344018

### Description

---

- Unique split-tip design penetrates through steel faster
- Resists walking or skidding, even on round surfaces
- Balanced, double-flute construction requires less pressure, does the work for you
- Designed and manufactured in USA.

### Specifications

---

- Bit Extension : 901
- Capacity : Cut Up Through 3/8 IN (9.500 MM) Mild Steel, Copper, Brass,Aluminum, Wood, Plastic and Laminates
- Hole Size : 1/8 IN (3.200 MM), 5/32 IN (4.000 MM), 3/16 IN (4.800 MM), 7/32 IN (5.600 MM), 1/4 IN (6.400 MM), 9/32 IN (7.100 MM), 5/16 IN (7.900 MM), 11/32 IN (8.700 MM), 3/8 IN (9.500 MM), 13/32 IN (10.300 MM), 7/16 IN (11.100 MM), 15/32 IN (11.900 MM), 1/2 IN (12.7
- Maximum Material Thickness : 10 GA (3.500 MM)
- Minimum Chuck Size : 3/8 IN (9.500 MM)
- Overall Length : 3-7/8/ IN (85.700 MM)
- Sub Brand : Kwik Stepper
- Type : Multi Hole