

05.53.033

Length
Material
Plating
Inside Diameter
Outside Diameter
Model
Type
Attribute
Design

**Round Spacer / Wall Thickness 1,4
3,2/6x3 Brass nickel plated**

3,0 mm
Brass QQ-B-6261 ASTM-B-16
Nickel plated
for M3= Dia. 3.0-3.5
6,00 mm
Spacer - Metall
Standard, Endsite Plain
3.2mm
Machine-cut
RoHS II compliant / Reach SVHC frei

