

SOLID PC 3819 13 T-2FSH



Sample photo

Order symbol: PC 3819 13 T-2FSH
Product nbr: 2539543
Description: Enclosure, PC
Remarks: Transparent hinged cover

EAN: 6418074052858
El. number:
Finland: 3435750
Sweden: 2539543
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm: 378	188	130		Ingress Protection (EN 60529): IP 65
inch: 14.9	7.4	5.1		Impact Resistance (EN 62262): IK 08/09
Materials:				Electrical insulation: Totally insulated
Material:	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035			UV resistance: UL 508
Cover colour:	Clear transparent			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:	Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:	Grey			UL Type: UL TYPE 1, 3, 3S, 12
Gasket material:	Polyurethane			Certificates:
Temperatures:				Underwriters Laboratories
Short term:	-40 ... 120 °C			Fimko
Continuous:	-40 ... 80 °C			Europe EN 62208: 2003
Short term:	-40 ... 250 °F			UL Canada
Continuous:	-40 ... 175 °F			Gost R
Accessories:				
EKMVT	Mounting plate			
EKMXT	Mounting plate Pertinax			
EKV 12	DIN-35 Mounting rail			
EKV 32	DIN-35 Mounting rail			
EKMZR	Extension frame			

SOLID 378x188x130-180

