





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	02/12/01	MCCORMICK
B	ECN# 2698: REVISED SHEET TOLERANCE	01/17/07	MCCORMICK



DB9F	DB9M
PIN 1	PIN 1
PIN 2	PIN 3
PIN 3	PIN 2
PIN 4	PIN 4
PIN 5	PIN 5
PIN 6	PIN 6
PIN 7	PIN 7
PIN 8	PIN 8
PIN 9	PIN 9



OUTLINE DRAWING

NOTES:

1. THIS D-SUBMINIATURE DB9 ADAPTOR HAS PHOSPHOR BRONZE FEMALE CONTACTS (SOCKETS) ON ONE SIDE AND BRASS MALE PINS ON THE OTHER SIDE. ALL CONTACTS ARE GOLD PLATED OVER NICKEL. COMPLETE 360° SHIELDING IS ACCOMPLISHED BY SOLDERING A STEEL STRIP (TIN PLATED) BETWEEN THE FLANGES OF THE TWO CONNECTORS.
2. EXPOSED STEEL SURFACES ARE TIN PLATED, AND JACKSCREWS ARE NICKEL PLATED.
3. CONNECTOR INSULATORS ARE GLASS FILLED PBT.
4. ADAPTER IS FULLY POPULATED WITH PINS AND SOCKETS. WIRING IS STRAIGHT THROUGH PIN FOR PIN, EXCEPT THAT WIRING OF PINS 2&3 IS REVERSING (SEE WIRING DIAGRAM)
5. LABEL; PANTONE 2945 BLUE. "L-COM" FONT MyriaMM ITALIC. "REVERSER" FONT ARIEL BOLD. TEXT HEIGHTS; .085", TEXT COLOR; WHITE

DIMENSIONS ARE IN INCHES [mm]
 UNLESS OTHERWISE SPECIFIED,
 TOLERANCES TO BE:
 .X ±.1 [2.5] ANGLES ±2°
 .XX ±.01 [.25]
 .XXX ±.005 [.13]
 OVERALL CABLE LENGTH TOL:
 ≤ 60 [1524] +3 [76.2] / - 0
 > 60 [1524] +5% / -0%



APPROVALS	DATE
DRAWN BY C.McCORMICK	02/12/01
CHECKED BY D.PARHAM	02/16/01
APPROVED BY R.CARRICK	02/13/01

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY D-SUBMINIATURE			
PRODUCT DESCRIPTION SOCHET SAVER ASSEMBLY			
SIZE A	FSCM NO. 43321	DWG. NO. DMA030MF-OD1	REV. B
SCALE: NONE CAD FILE: DMA030MF-OD1.SLDDRW			SHEET 1 OF 1