



T&B®

Rigid/IMC Conduit Fittings-Hazardous Location T&B Catalog Number:

UPC Number: GAT-4
Status: 04226945385
Description: Active

1/2 in. Male to Female Union, Die Cast Aluminum. For hazardous and non-hazardous locations.

Features

Precision cast and machined surfaces permit safer wire pulling.

Precision NPT threaded hubs allow trouble-free field installation for rigid or IMC conduit.

Die cast construction and industrial design combine to produce a rugged protective enclosure for devices on industrial and OEM applications.

Application

Junction for branch conduits in hazardous locations.

General

Material	Die Cast Aluminum
Volume (cu.in.)	28.0
Cover Opening (inches)	3 29/32

Dimension Information

Hub Size (inches)	1 1/4
Dimension A (inches)	4 5/16
Dimension B (inches)	3
Dimension C (inches)	3 11/16
Dimension D (inches)	2 1/16
Dimension E (inches)	1 1/32
Dimension F (inches)	7/8
Dimension G (inches)	5 11/16
Dimension J (inches)	4 9/16
Dimension K (inches)	3 15/16
Dimension L (inches)	5/8

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	1
Package in Units	5
T&B Sold in UOM	Each
T&B Weight Per UOM	216 lbs. per 100

Notes

*Note	Class I, Div. 1&2, Groups C, D - Explosionproof
**Note	Class II, Div. 1, Groups E, F, G - Dust-Ignitionproof
***Note	Class III, Div. 1&2 - Raintight
****Note	NEMA 3, 4, 7 CD, 9 EFG - Wet Locations

Certifications

RoHS Compliance No

Certifications



File Nbr:

E 35010

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com