



T&B®

Rigid/IMC Conduit Fittings-Hazardous Location T&B Catalog Number:

UPC Number: GUAB14-TB
Status: 78621034438
Description: Active

1/2 in. GUAB Hazardous location Conduit Outlet Box, Box-Ductile Iron-Zinc Plated, Cover-Die Cast Aluminum, 6.9 cu.in.

Features

All hubs have a minimum of five full threads and integral bushing

All boxes are furnished with internal grounding screw.

Application

GUA boxes can be used for hazardous location conduit runs for the following: (1) Allows for mounting of fixture outlets when used with appropriate covers; (2) Provides easy access to wiring; (3) Provides junction in conduit for wire pulling and splices; (4) Changes direction in rigid conduit systems; (5) Attaches two or more pieces of conduit long runs; (6) Guards against damage to wires in rigid conduit.

General

Material	Ductile Iron
Finish	Zinc Plated
Volume (cu.in.)	6.9

Dimension Information

Hub Size (inches)	1/2
Dimension A (inches)	2 1/4
Dimension B (inches)	2 1/2
Dimension C (inches)	7/8
Throat Diameter-Max (inches)	0.610
Throat Diameter-Min (inches)	0.570

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	173.9 lbs. per 100

Notes

*Note	Class I, Div. 1&2, Groups C, D - Explosionproof
**Note	Class II, Div. 1, Groups E, F, G - Dust-Ignitionproof
***Note	Class III, Div. 1&2 - Raintight
****Note	NEMA 3, 4, 7 CD, 9 EFG - Wet Locations

Certifications

RoHS Compliance	No
-----------------	----

Certifications



File Nbr:
E 202368

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com