

REMOTE AND VOLUME CONTROLS



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7

Home Theater

Volume Controls

Retail Part No.	Figure No.	Description	Color	Specifications
30-315	1	Cabinet Mounting Type	Black	15 watts audio. For use with 8-16 ohm speakers. Mono "L" pad
30-316	2	Cabinet Mounting Type	Black	15 watts audio. For use with 8-16 ohm speakers. Stereo "LL" pad
30-364	3	Wall Mounting Type	Black	10 watts peak audio. For use with 8-16 ohm speakers. Single "L" pad
30-372	3	Wall Mounting Type	Black	10 watts peak audio. For use with 8-16 ohm speakers. Stereo "LL" pad
65-1530	4	10 Step Stereo Volume Control-Standard	White	25 watts rms, 75 watts (avg), 8 ohms, 35Hz-20kHz, 30dB(max).10 switch steps
65-1620	5	10 Step Stereo Volume Control-Décor	White	25 watts rms, 50 watts (avg), 8 ohms, 20Hz-20kHz, 30dB(max).10 switch steps
65-3610	6*	12 Step Adj. Impedance Vol. Control-Standard	White	216 watts (max), 4-8 ohms, 35Hz-20kHz, 42dB in 12 steps, 3dB in 6 steps
65-3611	6*	12 Step Adj. Impedance Vol. Control-Standard	Ivory	216 watts (max), 4-8 ohms, 35Hz-20kHz, 42dB in 12 steps, 3dB in 6 steps
65-3635	6*	12 Step Adj. Impedance Vol. Control-Décor	Ivory	216 watts (max), 4-8 ohms, 35Hz-20kHz, 42dB in 12 steps, 3dB in 6 steps
65-3636	6*	12 Step Adj. Impedance Vol. Control-Décor	White	216 watts (max), 4-8 ohms, 35Hz-20kHz, 42dB in 12 steps, 3dB in 6 steps

*Requires 4" deep box

Remote Control

Retail Part No.	Figure No.	Description	Color	Specifications
65-2000	7	Universal Learning Remote Control	Silver	Backlit Touch Screen Control of 16 Devices with "Teach" Functions

For the latest information—www.gcelectronics.com
All quantities are single; BU's are packages of 10 Unless otherwise noted.