


REVISIONS	
ISS	DESCRIPTION\DATE

RoHS COMPLIANT



TITLE: BNC MALE TO DOUBLE FEMALE
Y STYLE

PART NO: BNC26

DRAWING NO: 20017-005(A003Y000)

030

APRD:	UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 >6-30 = ±0.4 >30-120 = ±0.6 >120-315 = ±1 >315-1000 = ±1.6 ANGLES = ±5°		SHELL	BRASS	NICKEL	
CHKD:			WASHER	STEEL	NICKEL	
			SPRING	STEEL	NICKEL	
			C RING	STEEL	NICKEL	
DR:			GASKET	RUBBER	RED	
			CONTACT PIN	BRASS	GOLD	
			INSULATOR	DELRIN	WHITE	
DATE: 07/19/12”		UNIT: mm		BODY	BRASS	NICKEL
SHEET: .		SCALE: 2/1	NO.	DESCRIPTION	MATERIAL	FINISH

ISO 9001 certificate