

THB.391.A4A

TeeTube Mini 4 Pole Screw - end barrier contact 7mm to 12mm, 4 mm max conductor size IP68 32A 450V 2 cable entries



compact design



Ø 23 mm



compact design



68 mm



PRODUCT SPECIFICATIONS

Temperature "T" rating	T125
Minimum cable diameter (mm)	7
Maximum cable diameter (mm)	12
Fixing system	Cable
Cable entries	2
Number of poles	4
Terminal type	Screw - end barrier contact
Body material	PA66 / PBT / TPE
Max conductor size (Sq mm)	4
Max current (A)	32
Max voltage (V)	450
Minimum temp rating °C	-40
Max temp rating °C	125
IP rating	68