

CD-196USB - CD Player



Professional DJ CD and MP3 player, with USB 2.0 interface, anti-shock system and remote control.

- USB storage media can be connected directly (e.g. USB hard disk, USB flash drive)
- Supports multi-partitions FAT16/FAT32, NTFS, HFS+
- Folder navigation
- ID3 tag analysis
- Supports playlists
- Pitch control: $\pm 8/\pm 16/\pm 100$ %
- Pitch bending
- Master tempo
- Search function via jog dial
- Scratch function
- Title programming for 99 tracks
- Smallest search step: 1 frame
- Automatic or manual beat counter, switchable
- Switchable display of the running time of one track as well as the remaining running time of one or all tracks
- Bar graph display
- Quick start (automatic cue)
- Fader start
- Digital output, coaxial
- 482 mm (19") rack installation
- Supplied with infrared remote control
- Audio CD/CD-R/MP3 CD

Technical data

General information

	:
Frequency range	: 20-20,000 Hz
THD	: < 0.1 %
Channel separation	: > 75 dB
Dynamic range	: > 80 dB
S/N ratio	: > 75 dB
Wow and flutter	: not measurable, quartz precision
Output, analogue	: 2 V
Output, digital	: 0.5 V _{pp} S/PDIF
Power supply	: 230 V~/50 Hz/15 VA
Admiss. ambient temp.	: 0-40 °C
Dim., player mech.	: 482x90x270 mm, 2 RS
Dim., control panel	: -
Weight	: 4.4 kg

Connections

	:
Analogue output	: 1 x RCA L/R
Digital output	: 1 x RCA
Fader start	: 1 x 3.5 mm jack
Control connection	: -