



Hand-Held Digital Thermometer FM35

The FM35 is a simple to use hand-held food thermometer featuring a large LCD display, rubber boot and On/Off key making it ideal for use in any food environment.

The instrument can be used with an option on probes to include general purpose and air probes to enable the user to quickly and accurately measure different temperature requirements. These are connected via a simple lumberg plug.

The FM35's protective rubber boot can prevent accidental damage if the instrument is dropped and is an essential part of any busy kitchen.

The FM35 comes complete with a general purpose probe.

Key Features

- Open probe indication.
- Lumberg connector.
- Long battery life.
- Rubber Boot

Accessories

Probes

- FM35-GP – FM35 General Purpose Probe.
Thermistor sensor. Coiled cable.
- FM35-AP – FM35 Fast Response Flexible Air Probe.
Thermistor sensor.

Test Caps

- FM35CC1 – Test cap, -18°C for FM35
- FM35CC2 – Test cap, 0°C for FM35
- FM35CC3 – Test cap, +70°C for FM35





Hand-Held Digital Thermometer FM35

Specification

Water Resistant	Yes
Auto Off	Yes (after 3 minutes)
Open Circuit Indication	Yes
Connector Type	Lumberg
Range	-40°C to 110°C/-40°F to 230°F
Accuracy	±0.5°C (0° to 70°C) ±1°C elsewhere/ ±0.9°F (32° to 158°C) ±1.8°F elsewhere
Battery	1x 9V included
Battery Life	3000 hours approx. continuous use

