



All TM units and accessories rated IP66/67

TM Heavy Duty Interlocked Switched Sockets. (Will accept both IP44 & IP67 plugs)



Part No.	Amps	Volts	Poles	HxW mm
TM1643SP	16	110	2P+E(3)	276 x 114
TM1663SP	16	230	2P+E(3)	276 x 114
TM1664SP	16	415	3P+E(4)	276 x 114
TM1665SP	16	415	3P,N+E(5)	277 x 114
TM3243KSP	32	110	2P+E(3)	285 x 114
TM3263KSP	32	230	2P+E(3)	285 x 114
TM3264KSP	32	415	3P+E(4)	285 x 114
TM3265KSP	32	415	3P,N+E(5)	285 x 114
TM6363SP	63	230	2P+E(3)	415 x 144
TM6364SP	63	415	3P+E(4)	415 x 144
TM6365SP	63	415	3P,N+E(5)	415 x 144

2009

TM Heavy Duty Interlocked Switched Sockets with compartment for RCD / MCB. (not supplied) c/w din rail and tails fitted. (Will accept both IP44 & IP67 plugs)

Part No.	Amps	Volts	Poles	HxW mm
TM1643IR	16	110	2P+E(3)	276 x 114
TM1663IR	16	230	2P+E(3)	276 x 114
TM1664IR	16	415	3P+E(4)	276 x 114
TM1665IR	16	415	3P,N+E(5)	277 x 114
TM3243KIR	32	110	2P+E(3)	285 x 114
TM3263KIR	32	230	2P+E(3)	285 x 114
TM3264KIR	32	415	3P+E(4)	285 x 114
TM3265KIR	32	415	3P,N+E(5)	285 x 114
TM3243IR	32	110	2P+E(3)	398 x 144
TM3263IR	32	230	2P+E(3)	398 x 144
TM3264IR	32	415	3P+E(4)	398 x 144
TM3265IR	32	415	3P,N+E(5)	398 x 144
TM6363IR	63	230	2P+E(3)	415 x 144
TM6364IR	63	415	3P+E(4)	415 x 144
TM6365IR	63	415	3P,N+E(5)	415 x 144

Special Docks Use - Refrigerated Containers - ISO standard. 3 o'clock earth. Compartment for RCD.

Part No.	Amps	Volts	Poles	HxW mm
TM3234KIR	32	415	3P+E(4)	285 x 114
TM3234IR	32	415	3P+E(4)	398 x 144



Modular accessories for the TM range of switched sockets



Modular Back Box

TM2344T2

Predisposed to accommodate 2x16A or 2x32A(K) TM switched interlocks.

TM3444T3

Predisposed accommodate 3x16A or 3x32A(K) TM switched interlocks.



Hinged Top Covers

TM2318R2

c/w din rail kit. Will accommodate 10 modules (mcb/s)

TM3418R3

c/w din rail kit. Will accommodate 16.5 modules (mcb/s)

Fixed Top Covers

TM2318P2

c/w din rail kit. Will accommodate 10 modules (mcb/s)

TM3418P3

c/w din rail kit. Will accommodate 16.5 modules (mcb/s)

Fixed Bottom Cover

TM1125P

To cover unused space in bottom half of modular back box

SQE (IP44) Interlocked Switched Socket



Part No.	Amps	Volts	Poles
SQE1643C	16	110	2P+E(3)
SQE1663C	16	230	2P+E(3)
SQE1664C	16	415	3P+E(4)
SQE1665C	16	415	3P,N+E(5)
SQE3263C	32	230	2P+E(3)
SQE3264C	32	415	3P+E(4)
SQE3265C	32	415	3P,N+E(5)

SQE (IP55) Interlocked Switched Socket



Part No.	Amps	Volts	Poles
SQE1643.5C	16	110	2P+E(3)
SQE1663.5C	16	230	2P+E(3)
SQE1664.5C	16	415	3P+E(4)
SQE1665.5C	16	415	3P,N+E(5)
SQE3263.5C	32	230	2P+E(3)
SQE3264.5C	32	415	3P+E(4)
SQE3265.5C	32	415	3P,N+E(5)

SQE (IP44) Interlocked Switched Socket with compartment for RCD (not supplied) c/w din rail (not fitted)



Part No.	Amps	Volts	Poles
SQE1643FM	16	110	2P+E(3)
SQE1663FM	16	230	2P+E(3)
SQE1664FM	16	415	3P+E(4)
SQE1665FM	16	415	3P,N+E(5)
SQE3243FM	32	110	2P+E(3)
SQE3263FM	32	230	2P+E(3)
SQE3264FM	32	415	3P+E(4)
SQE3265FM	32	415	3P,N+E(5)

SQE (IP55) Interlocked Switched Socket with compartment for RCD (not supplied) c/w din rail (not fitted)



Part No.	Amps	Volts	Poles
SQE1643.5FM	16	110	2P+E(3)
SQE1663.5FM	16	230	2P+E(3)
SQE1664.5FM	16	415	3P+E(4)
SQE1665.5FM	16	415	3P,N+E(5)
SQE3243.5FM	32	110	2P+E(3)
SQE3263.5FM	32	230	2P+E(3)
SQE3264.5FM	32	415	3P+E(4)
SQE3265.5FM	32	415	3P,N+E(5)



FM replacement back box for SQE units. To allow fitting of RCD in compartment above.

Part No.

FM1043SQV



SQ (IP44) Interlocked Switched Socket

Part No.	Amps	Volts	Poles
SQ1643C	16	110	2P+E(3)
SQ1663C	16	230	2P+E(3)
SQ1664C	16	415	3P+E(4)
SQ1665C	16	415	3P,N+E(5)

Enclosures for RCDs/MCBs, with hinged cover.



Boxes with fixed covers



Part No.	Dimensions mm
TM1114GB	Room for 4 modules. 115w x 144h x 120d
TM1414GB	Room for 5.5 modules. 144w x 144h x 120d
TM2314GB	Room for 10.5 modules. 230w x 144h x 120d
TM2614GB	Room for 12 modules. 260w x 144h x 120d
TM2914GB	Room for 13.5 modules. 290w x 144h x 120d

Part No.	Dimensions mm
TM1114DB	115w x 144h x 94.5d
TM1414DB	144w x 144h x 94.5d
TM2314DB	230w x 144h x 94.5d
TM2614DB	260w x 144h x 94.5d
TM2914DB	290w x 144h x 94.5d