























SxP Soldering & Rework Cartridges



Compatible with: MFR-1110, MFR-1161, MFR-1351, MFR-2211, MFR-2241 Systems and MFR-H1-SC hand-piece

| SxP SOLDERING & REWORK CARTRIDGES | | | | | |
|-----------------------------------|---|--|--|--|--|
| CHISEL |  | SFP-CH10 STP-CH10 SCP-CH10 | CONICAL |  | SFP-CN04 STP-CN04 SCP-CN04 |
| |  | SFP-CH15 STP-CH15 SCP-CH15 | |  | SFP-CNB04 STP-CNB04 SCP-CNB04 |
| |  | SFP-CHB15 STP-CHB15 SCP-CHB15 | |  | SFP-CNL04 STP-CNL04 SCP-CNL04 |
| |  | SFP-CH20 STP-CH20 SCP-CH20 | |  | SFP-CN05 STP-CN05 SCP-CN05 |
| |  | SFP-CHL20 STP-CHL20 SCP-CHL20 | |  | SFP-CNB05 STP-CNB05 SCP-CNB05 |
| |  | SFP-CH25 STP-CH25 SCP-CH25 | |  | SFP-CNL06 SCP-CNL06 |
| |  | SFP-CH30 STP-CH30 SCP-CH30 | |  | SFP-BVL10 STP-BVL10 SCP-BVL10 |
| |  | SFP-CH35 STP-CH35 SCP-CH35 | |  | SFP-DRH05 STP-DRH05 SCP-DRH05 |
| |  | SFP-CH50 STP-CH50 SCP-CH50 | |  | SFP-DRH610 STP-DRH610 SCP-DRH610 |
| | | | |  | SFP-DRH15 STP-DRH15 SCP-DRH15 |
| | |  | SFP-DRH615 STP-DRH615 SCP-DRH615 | | |
| | |  | SFP-DRH35 STP-DRH35 SCP-DRH35 | | |
| | |  | SFP-DRK50 STP-DRK50 SCP-DRK50 | | |
| | | KNIFE | | | |

F = FR4 / Fiber Glass, for most standard applications T = Temperature Sensitive C = Ceramic for high thermal demand applications.