



Ty-Fast®

TY100-18

All-plastic cable tie for multi purpose use.

T&B Catalog Number: **TY100-18**
EAN Number: 05414363060215
UPC Number: 78621059650
Description: All-plastic, standard cable tie, 112 x 2.4 mm, natural Polyamide 6.6



Technical Information

Type	standard
Material	Polyamide 6.6
Temperature Range	-40°C to +85°C
Flammability Rating	UL 94 V-2
Colour	natural
Halogen free	yes
Silicone free	yes

Approvals

UL recognised	E49405
Germanischer Lloyd approval	yes
Lloyds Register approval	yes
Other approval	BVQ

Ordering Information

Length (mm)	112
Width (mm)	2.4
Max. Bundle Diameter (mm)	25
Min. Bundle Diameter (mm)	1.6
Min. Tensile Strength (N)	80
Quantity (pieces)	1000
Packaging Type	bag

Storage Conditions

Nylon (Polyamide) is inherently susceptible to environmental conditions. Polyamide 6.6 cable ties are moisturised to optimum performance levels at machine-side and should be stored in cool dry areas out of direct sunlight. Cable ties are packaged in plastic bags to contain moisture and should remain sealed until ready for use.

Tooling

ERG50, WT193A
