

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Hand and Head Torches
Catalogue number	9510, 9520, 9610, 9620
Date	30/01/2014

Range Description

Hand and Head Torches

Features

9510

- High power 120 lumen CREE XR-E Q5 LED
- 3 lighting modes: High, Dimmed, Flash
- One-handed Rapid Slide Focus mechanism (RSF) - Spot (x1) to Flood (x10)
- Beam intensifying plano-convex optical lens
- Robust high grade aluminium body
- Water & dirt resistant, tested to IP64
- Battery life: High - 6hrs, Dimmed - 16hrs
- Battery 3 x AAA (Not supplied)



9520

- High power 150 lumen CREE XR-E Q5 LED
- 3 lighting modes: High, Dimmed, Flash
- One-handed Rapid Slide Focus mechanism (RSF) - Spot (x1) to Flood (x30)
- Beam intensifying plano-convex optical lens
- Robust high grade aluminium body
- Water & dirt resistant, tested to IP64
- Battery life: High - 5hrs, Dimmed - 14hrs
- Battery 3 x AAA (Not supplied)



9610

- High power 120 lumen CREE XR-E Q3 LED
- 3 lighting modes: High, Dimmed, Flash
- One-handed Rapid Slide Focus mechanism (RSF) - Spot (x1) to Flood (x7)
- Beam intensifying plano-convex optical lens
- Robust high grade aluminium lamp body
- Adjustable head lamp swivels through 90°
- Water & dirt resistant, tested to IP64
- Battery life: High - 5hrs, Dimmed - 13hrs
- Battery 3 x AAA (Not supplied)



9620

- High power 200 lumen CREE XM-L T6 LED
- 3 lighting modes: High, Dimmed, Flash
- One-handed Rapid Slide Focus mechanism (RSF) - Spot (x1) to Flood (x7)
- Beam intensifying plano-convex optical lens
- Robust high grade aluminium lamp body
- Adjustable head lamp swivels through 90°
- Detachable head lamp & battery pack
- Water & dirt resistant, tested to IP64
- Battery life: High - 5hrs, Dimmed - 12hrs
- Battery 4 x AA (Not supplied)



Item Number	Item Description	EAN No	Commodity code	Carton Qty
T9510	C.K CREE LED Hand Torch 120 Lumens	5013969977448	85131000	24
T9520	C.K CREE LED Hand Torch 150 Lumens	5013969977431	85131000	24
T9610	C.K CREE LED Head Torch 120 Lumens	5013969977462	85131000	24
T9620	C.K CREE LED Head Torch 200 Lumens	5013969977455	85131000	24

Technical product information					
		T9510	T9520	T9610	T9620
	Body material	Aluminium Alloy	Aluminium Alloy	Aluminium Alloy	Aluminium Alloy
	LED lifetime	100,000hrs	100,000hrs	100,000hrs	100,000hrs
Maximum range	250m	150m	200m	250m	
Standards compliance	None applicable				
User health and safety information	None applicable				
RoHS/WEEE compliance	This product range is fully Compliant with the RoHS and WEEE regulations				
Material safety data	None applicable				
Warranty	36 months				
Country of origin	China				

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T9510	40	40	133	169	160	125	40	138
T9520	30	30	107	104	205	135	55	223
T9610	-	-	-	91	175	165	95	132
T9620	-	-	-	226	240	190	90	294

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T9510	160	140	200			
T9520	180	180	220			
T9610	310	180	180			
T9620	430	250	190			

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T9510	23	Clamshell	10	Card			50	box
T9520	31	Clamshell	10	Card			60	box
T9610	32	Clamshell	15	Card			72	box
T9620	57	Clamshell	16	Card			84	box