

datasheet for AK 2 S
article number: 932146100

| | |
|--|--|
| product description: | order number: 932 146-100 |
| description: | Insulated, high strength alligator clip. Clamping range up to 9.5 mm bolt diameter. The flat part of the jaws (fine wire section) allows even the finest wires to be clamped. 4 mm diameter socket connection and screw connection up to 1.5 mm ² . |
| typ: | AK 2 S schwarz/black |
| system: | 4mm system |
| order number: | 932 146-100 |
| clamping range: | 9.5 mm |
| color | |
| other color versions: | |
| technical data | |
| measurement category acc. to IEC 61010: | CAT I |
| type of contact: | clamp |
| type of termination: | 4 mm socket (unsprung), screw |
| rated voltage: | 30 VAC / 60 VDC |
| rated current: Please consider derating curve! | 25 A |
| contact resistance: | 10 mOhm |
| material | |
| contact material: | brass |
| contact surface material: | nickel |
| housing material: | PP |
| environmental conditions: | |
| temperature range: | -25 °C to +80 °C |
| flammable class: | |
| housing (basic material): | UL 94 HB |
| drawing | |