

## MINIATURE LAMP (1891) Details



Part #	1891				
Description	T3 1/4 M BAY 14V .24A 2CP				
Bulb Shape	T-3 1/4	Filament	C-2F	Base Style	Miniature Bayonet (BA9s)
Glass Diameter (in)	0.39	MOL <sup>†</sup> (in)	1.19	LCL <sup>††</sup> (in)	0.56
Glass Diameter (mm)	10	MOL (mm)	30.23	LCL (mm)	14.22
Volts	14	MSCP <sup>‡</sup>	2	Avg Life Hrs	500
Watts	3.36	Amps	0.24	RoHS Compliant	

### <sup>†</sup> MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

### <sup>‡</sup> MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

### <sup>††</sup> LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.