

MINIATURE LAMP (7371) Details



| Part # | 7371 | | | | |
|---------------------|-----------------------------|-----------------------|-------|------------------------|------------|
| Description | T1 3/4 BIPIN 12V .04A .12CP | | | | |
| Bulb Shape | T-1 3/4 | Filament | C-2F | Base Style | G-4 Bi-Pin |
| Glass Diameter (in) | 0.22 | MOL [†] (in) | 0.63 | LCL ^{††} (in) | 0.50 |
| Glass Diameter (mm) | 5.5 | MOL (mm) | 16.00 | LCL (mm) | 12.70 |
| Volts | 12 | MSCP [‡] | 0.12 | Avg Life Hrs | 20000 |
| Watts | 0.48 | Amps | 0.04 | RoHS Compliant | |

† MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.