

MINIATURE LAMP (PR2) Details



Part #	PR2				
Description	PR BULB 2.38V .5A .80CP				
Bulb Shape	B-3 1/2	Filament	C-2R	Base Style	S.C. Miniature Flanged
Glass Diameter (in)	0.43	MOL[†] (in)	1.25	LCL^{††} (in)	0.25
Glass Diameter (mm)	11	MOL (mm)	31.75	LCL (mm)	6.35
Volts	2.38	MSCP[‡]	0.8	Avg Life Hrs	15
Watts	1.19	Amps	0.50	RoHS Compliant	

† MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.