

## Kvaser Leaf Light HS



- The Kvaser Leaf Light supports full speed USB interface for CAN with high performance at a low cost.
- Kvaser Leaf Light is a reliable low cost product. Loss free transmission and reception of standard and extended CAN messages on the CAN bus is transmitted with a time stamp precision of 100 microseconds.
- The low current consumption, 70 mA, reduces the power drain from your laptop. Application Areas: Human Interfaces, testing equipment, different types of one channel tools, multi channel tools not requiring channel synchronization, etc.



## Technical Data

### Kvaser Leaf Light HS

Galvanic Isolation	No
Bitrate	5-1000 kbit/s
Silent mode	No
Error frame generation	No
Error frame detection	Yes
Weight	100g
Timestamp resolution	100 s
On board buffer	Yes
Maximum message rate, send	8000
Maximum message rate, receive	8000
Sound	No
Clock synchronization	N/A
Dimensions (WxLxH)	25x100x20mm
Temperature range	-20 C to +75 C
Order number	73-30130-00241-8

The information herein is subject to change without notice