#### Circuit Guard®

Commercial Grade, Portable Ground Fault

#### Hubbell Tough, Hubbell Safe!

#### Field Wireable

The Circuit Guard commercial grade plug is available in automatic reset and manual reset versions. The product features three cable grommets for proper strain relief. The housing is constructed of high strength polycarbonate material.



#### **Single Outlet Portable Line Cords**

Single outlet line cords are available in manual and automatic reset versions. Line cords may be ordered in two foot or twenty-five foot lengths.

#### **Triple-Tap Portable Line Cords**

Triple-tap line cords may be ordered in two foot and twenty-five foot lengths. Line cords are available in both manual reset and automatic reset models. Manual reset models are recommended for safe-start applications.

#### **OEM Equipment Integrated Cord Sets**

Cord sets feature black cord with flying leads on one end. These replacement cord sets are available in fifteen foot and thirty-five foot lengths. Cord sets may be ordered in either manual or automatic reset versions.



#### **Features**

- Automatic or manual reset (safe-start) versions.
- Meets OSHA regulations for open neutral relay protection.
- High reliability mechanical flag indicates ground fault and power status.
- Raintight NEMA 3R housing is rated for indoor and outdoor use.
- Internal o-rings seal around test and reset buttons.
- Strain relief grommets fit #12 AWG through #18 AWG cord.
- Line cords feature high visibility, tough, yellow 12/3 SJEOW cord.
- OEM cord sets feature black cord and stripped wire leads. Cord is high flex 14/3 SJEOOW.
- cULus listed class A GFCI protection.



## Circuit Guard®

# Commercial Grade, Portable Ground Fault













### **Commercial Grade GFCI Product Offering** GFP515A **GFP2CA GFP2TTM**

	•	
Catalog Number	Description	Length
<b>Commercial Grade</b>	Commercial Grade GFCI Plug (Field Wireable)	
GFP515A	15A 120V AC, GFCI Plug, Automatic Reset	n/a
GFP515M		n/a
<b>Commercial Grade</b>	Commercial Grade GFCI Line Cord Single Outlet	
GFP2CA	15A 120V AC, GFCI Line Cord, Automatic Reset	νī
GFP2CM	15A 120V AC, GFCI Line Cord, Manual Reset	νī
GFP25CA	15A 120V AC, GFCI Line Cord, Automatic Reset	25
GFP25CM	15A 120V AC, GFCI Line Cord, Manual Reset	25'
<b>Commercial Grade</b>	GFCI Line Cord with Triple Tap	
GFP2TTA	15A 120V AC, GFCI Triple Tap Line Cord, Automatic Reset	νī
GFP2TTM	15A 120V AC, GFCI Triple Tap Line Cord, Manual Reset	7
GFP25TTA	15A 120V AC, GFCI Triple Tap Line Cord, Automatic Reset 25	25'
GFP25TTM	15A 120V AC, GFCI Triple Tap Line Cord, Manual Reset	25'
<b>Commercial Grade</b>	Commercial Grade OEM Equipment Integrated Cord Sets	
GFP15LA	15A 120V AC, GFCI w/ Flying Leads, Automatic Reset	15'
GFP15LM	15A 120V AC, GFCI w/ Flying Leads, Manual Reset	15'
GFP35LA	15A 120V AC, GFCI w/ Flying Leads, Automatic Reset	35
GFP35LM	15A 120V AC, GFCI w/ Flying Leads, Manual Reset	35

## Also from Hubbell...

Hubbell also offers a complete line of 30A, 120, 240 and 120/240 Volt permanent and portable GFCI products. Please visit www. hubbellcatalog.com/wiring for more information.













GFP15M

GFP5266CY

# **Industrial Grade Product Offering**

Catalog Number	<b>D</b> escription Le	Length
<b>Industrial Grade F</b>	Portable GFCI Line Cords Straight Blade	
GFP4C15A	set	18"
GFP4C15M		8
GFP6C15A	set	ගු
GFP6C15M	15A 120V AC, GFCI Line Cord, Manual Reset	ගු
GFP25C15A	15A 120V AC, GFCI Line Cord, Automatic Reset	25
GFP25C15M	15A 120V AC, GFCI Line Cord, Manual Reset	25
GFP3C20M	20A 120V AC, GFCI Line Cord, Manual Reset	ယ္
GFP50C15WM	15A 120V AC, GFCI Line Cord, Manual Reset	50 <sup>.</sup>
GFP100C15WM	15A 120V AC, GFCI Line Cord, Manual Reset	100'
GFP3C15MTL	15A 120V AC, GFCI Line Cord, Manual Reset, Twist-Lock®	ω
GFP3C20MTL	20A 120V AC, GFCI Line Cord, Manual Reset, Twist-Lock®	ယ္
Industrial Grade (	Industrial Grade OEM Equipment Integrated Cord Sets	
GFPOEMM	15A 120V AC, GFCI w/ Flying Leads, Manual Reset	15
GFPOEMA	15A 120V AC, GFCI w/ Flying Leads, Automatic Reset	10'
Portable Plug-In,	GFCI Tester, Multi-Outlet Portable, & GFCI Module	
GFP315A	15A 120V AC, GFCI 3-Outlet Plug-In	n/a
GFT2G	20A 120V AC, GFCI Tester (Measures leakage 1-7 mA)	n/a
GFP15M	15A 120V AC, Heavy Duty 4-Outlet Portable GFCI	<u>ත</u>
GFP20M	20A 120V AC, Heavy Duty 4-Outlet Portable GFCI	<u>ත</u>
GFM20	20A 120V AC, NEMA 3R GFCI Module Manual Reset	n/a
Industrial Grade (	Industrial Grade GFCI Plug and Line Cord	
GFP5266CY	15A 120V AC, GFCI Plug, Manual Reset, Yellow	n/a
GFP5266C	15A 120V AC, GFCI Plug, Manual Reset, Black	n/a
GFP1C	15A 120V AC, GFCI Line Cord with GFP5266CY Plug	<u>-</u>

