

**H0,34/10 TK SV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- in multipack bag (5 x 100 pcs.)
- Weidmüller colour code

**General ordering data**

Type	H0,34/10 TK SV
Order No.	<a href="#">9026030000</a>
Version	Wire end ferrule, 0.34 mm <sup>2</sup> , 6 mm, Colour code: Weidmüller, Turquoise (RAL 5018)
GTIN (EAN)	4008190177171
Qty.	500 pc(s).

**Data sheet**

**H0,34/10 TK SV**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	10 mm	Net weight	0.054 g
--------	-------	------------	---------

**Product data**

Conductor cross-section	0.34 mm <sup>2</sup>	Wire connection cross section AWG, max.	AWG 22
Contact surface length (L2)	6 mm	Contact surface diameter (D1)	0.8 mm
Collar diameter (D2)	2 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.25 mm		

**Classifications**

ETIM 3.0	EC000005	UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01	eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01		

**Approvals**

Approvals



ROHS Conform