


PRODUCT SPECIFICATION

Brand	C.K
Product Range	Centre punches
Catalogue number	3307, 3309 & 3326
Date	30/03/2010

Range Description Centre punches				
Features				
3307 <ul style="list-style-type: none"> Hardened carbon steel with gun metal finish for protection. Knurled shaft for grip 				
3319 <ul style="list-style-type: none"> Octagonal shank, hardened, chrome vanadium steel for professional performance 				
3326 <ul style="list-style-type: none"> Octagonal shank, hardened, chrome molybdenum steel for professional performance. Manufactured to DIN 7250 				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3307P	Centre Punch 100x10mm	5013969466607	82055990	12
T3319	Centre Punch 150x10mm	5013969468106	82055990	6
T3326	Centre Punch 120x12mm	5013969470109	82055990	6

Technical product information	
Standards compliance	None applicable
User health and safety information	Users are advised to wear eye protection when using striking tools
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K products are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Germany

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3307P	10	10	100	46	35	11	155	48
T3319	10	10	150	49	-	-	-	-
T3326	12	12	120	91	-	-	-	-

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3307P	93	155	63	618		
T3319	80	11	170	298		
T3326	75	13	140	550		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3307P	2	Wallet	-	-	-	-	42	Box
T3319	-	-	-	-	5	Bag	-	-
T3326	-	-	-	-	5	Bag	-	-