

For Patient-Care Areas - 4-outlet Medical-Grade Power Strip with 2-ft. Cord

MODEL NUMBER: PS-402-HG-OEM









Description

TrippLite's PS-402-HG-OEM Power Strip is designed to be installed on any mobilecart, diagnostic equipment, instrument, IV pole, etc. It is designed to supplypower to plug-connected components of a movable equipment assembly that israck-, table- or pedestal-mounted. Features 4 output receptacles, 2-ft. ACpower cord and two built-in resettable circuit breakers that control power toall outlets and protect against overloads. Switchless design preventsaccidental shutoff. Optional-use keyhole mounting tabs and flanges.

PLUG/OUTLETS:NEMA 5-15P-HG hospital-grade plug and 4 NEMA5-15R-HG hospital-grade receptacles

ELECTRICAL:120V AC, 50/60Hz, 15A

FORMAT:All-metal corded multi-outlet strip

Features

- Versatile power distribution strip designed to be installed on any mobile cart, IV pole, etc.
- Meets UL 1363A to supply power to plug-connected components of a movable equipment assembly that is rack-, table- or pedestal-mounted
- 4 x NEMA 5-15R-HG hospital-grade output receptacles
- 2-ft. AC cord with integrated, molded NEMA5-15P-HG hospital-grade plug
- · Rugged all-metal housing withstands years of use without breakage
- 15A electrical capacity with two built-in resettable circuit breakers
- 120V, 50/60Hz
- Optional-use keyhole mounting tabs and flanges
- Switchless design prevents accidental shutoff

Specifications

Highlights

- Designed to be installed on any mobile cart, IV pole, etc.
- Tested to UL 1363A to supply power to plug-connected components of a movable equipment assembly, that is rack-, table- or pedestal-mounted
- 4 hospital-grade receptacles and hospital-grade plug
- 2 ft. cord
- Two 15-amp resettable circuit breakers

Applications

- Mobile carts, IV poles and other UL 1363A certified usages.
- Can be used in Patient Care
 Areas, when properly mounted.

Package Includes

- PS-402-HG-OEM Power Strip
- Owner's manual and warranty information





OVERVIEW	
Intended Application	Hospital/Medical
Model Type	For Patient-Care Areas
OUTPUT	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Overload protection	2 x 15amp breakers (1 line, 1 neutral)
Outlet quantity / type	4 NEMA 5-15R-HG
Outlet orientation	Single row of 4
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input connection type	NEMA 5-15P-HG
Input cord length (ft.)	2
Input cord length (m)	4.572
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	No power switch
PHYSICAL	
Shipping Dimensions (HWD/in)	2.36 x 6.10 x 9.76
Shipping weight (lbs)	1.64
Unit Dimensions (HWD/in)	1.73 x 2.50 x 8.54
Unit weight (lbs)	1.45
Material of construction	Metal
Integrated keyhole mounting tabs	Keyhole mounting tabs and flanges enable mounting to a variety of surfaces
Receptacle Color	White
AC line cord color	White
Style	Strip
Outlets center to center measurement	Inner outlets = 32.5mm



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Keyhole slot center to center measurement	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm	
CERTIFICATIONS		
Approvals	TUV tested to UL 1363A	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.