


PRODUCT SPECIFICATION

Brand	C.K
Product Range	Wood Chisels
Catalogue number	1178, 1126
Date	01/06/2010

<p>Range Description Professional quality beveled edge wood chisels</p>				
<p>Features</p> <ul style="list-style-type: none"> • Hot drop forged chrome vanadium steel blades – for professional performance • Blades are full length hardened – for long life performance • Shatterproof acetate handles, deigned for use with a mallet or hammer, safe and tough • Protective blade covers – for protection when not in use • Set presented in convenient storage case and supplied complete with sharpening stone 				
Tem Number	Item Description	EAN No	Commodity code	Shelf box Qty
T1126	Sharpening stone, medium/fine silicone carbide 200x50mm	5013969069426	68043000	1
T1178 025	Bevelled edge wood chisel 6mm	5013969417708	82053000	3
T1178 037	Bevelled edge wood chisel 10mm	5013969417906	82053000	3
T1178 050	Bevelled edge wood chisel 13mm	5013969418002	82053000	3
T1178 062	Bevelled edge wood chisel 16mm	5013969418101	82053000	3
T1178 075	Bevelled edge wood chisel 19mm	5013969418200	82053000	3
T1178 087	Bevelled edge wood chisel 22mm	5013969418309	82053000	3

T1178 100	Bevelled edge wood chisel 25mm	5013969418408	82053000	3
T1178 125	Bevelled edge wood chisel 32mm	5013969418507	82053000	3
T1178 150	Bevelled edge wood chisel 38mm	5013969418606	82053000	3
T1180	Bevelled edge wood chisel set (6mm, 13mm, 19mm & 25mm (plus silicone carbide sharpening stone) complete with storage case	5013969068306	82053000	3

Technical product information	Sharpening stone grit – Silicone carbide, Fine side #240. Coarse side #150
Standards compliance	None applicable
User health and safety information	Users are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	Not applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T1126	50	25	200	422	53	27	235	438
T1178 025	25	25	260	137	70	32	360	176
T1178 037	25	25	260	144	70	32	360	183
T1178 050	25	25	260	159	70	32	360	198
T1178 062	25	25	260	169	70	32	360	208
T1178 075	25	25	260	178	70	32	360	217
T1178 087	25	25	260	186	70	32	360	225
T1178 100	25	25	260	209	70	32	360	248
T1178 125	32	25	260	252	70	32	360	291
T1178 150	38	25	260	302	70	32	360	341
T1180	–	–	–	–	185	48	385	1523

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g Inc product	No of cartons on base	Number of rows high
T1126	–	–	–	–		
T1178 025	80	380	80	635		
T1178 037	80	380	80	665		
T1178 050	80	380	80	710		
T1178 062	80	380	80	740		
T1178 075	80	380	80	767		
T1178 087	80	380	80	791		
T1178 100	80	380	80	860		
T1178 125	80	380	80	989		
T1178 150	80	380	80	1139		
T1180	190	410	165	4914		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T1126			16	Box				
T1178 025	18	Blister	21	Backing card			116	Box
T1178 037	18	Blister	21	Backing card			116	Box
T1178 050	18	Blister	21	Backing card			116	Box
T1178 062	18	Blister	21	Backing card			116	Box
T1178 075	18	Blister	21	Backing card			116	Box
T1178 087	18	Blister	21	Backing card			116	Box
T1178 100	18	Blister	21	Backing card			116	Box
T1178 125	18	Blister	21	Backing card			116	Box
T1178 150	18	Blister	21	Backing card			116	Box
T1180							345	Box