




P1 STRIPPED JACKET 35mm			
1	—————	TINNED 3mm	BLACK
2	—————	TINNED 3mm	WHITE
3	—————	TINNED 3mm	RED
4	—————	TINNED 3mm	YELLOW
5	—————	TINNED 3mm	PURPLE
6	—————	TINNED 3mm	BLUE
7	—————	TINNED 3mm	GREEN
8	—————	TINNED 3mm	BROWN
SHIELD	—————	TINNED 3mm	DRAIN

PART NO.	MD-3P	MD-4P	MD-5P	MD-6P	MD-7P	MD-8P
POSITION						

* NOTE: All relevant materials are complied with RoHS directive .

3	MOLDED PVC BLACK			M304
2	NON-UL 3C-8C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, JACKET BLACK,		Lmm	M304
1	MINI DIN 8 MALE, GOLD FLASH ON CONTACTS, BLACK INSULATOR		1	M108
No.	DESCRIPTION		Q'TY	Supplier
APPROVED			Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm	
CHECKED	HU			
DRAWING	JUDY			
DATE	08/MAY/12	ITEM NO.		
			UNIT:mm	