Shielded D-Sub Backshells DMVZK Series

TECHNICAL SPECIFICATIONS

Material: Zinc, Ni-plated
Temp. range: -40°C - 120°C
Cable strain relief: Cable clamp with 2

assembly screws

Cable diameter: 4.0 - 13.0 mm

Locking screws: Delivered with pre-mounted

UNC4-40 jackscrews. M2.5, M2.6

and M3.0 as option

Cable outlet: Angled


Attenuation factor: > 60 dB between 300 MHz


and 900 MHz











TYPE	Α	В
DMVZK9	32	39,5
DMVZK15	40,3	39,5

PART NUMBERING SYSTEM

	DMVZK9 F
Series: ————————————————————————————————————	
Size: ————	
9 & 15	
Thread (jackscrew): ————	
Omit = UNC 4-40	
M2.5	
M2.6	
M3.0	
Packaging: ————	
K = Kit package	

FEATURES

BULK = Bulk / 100 pcs

- Available in sizes 9- and 15-way
- Minimise interference from electromagnetic and RF sources
- Pre-mounted jackscrew provide easy assembly
- Non-static parts avoid ESD problems
- Accept round foil and braided cable types
- Approved according VDE 0871, FCC 20780 and 89/336/EU
- Company logotype available upon request
- Jackscrews with UNC 4-40 thread as standard, M2.5, M2.6 or M3.0 as option
- For custom designed solutions, please consult factory