

3 and 4-Wire *pico*fast® Field Wireable Connectors, Standard

- Female Connectors
- IEC IP 67 Protection



Drawing	Part Number	Specifications	Application	Pinout
	B 5131-0	PBT, Black Accepts 3-5 mm cable diameter Solder terminals, accepts up to 24 AWG conductors 85°C 60 VAC/ 75 VDC, 4 A	Mates with 3-pin threaded cordsets and receptacles	
	B 5141-0	PBT, Black Accepts 3-5 mm cable diameter Solder terminals, accepts up to 24 AWG conductors 85°C 30 VAC/ 36 VDC, 3.0 A	Mates with 4-pin threaded cordsets and receptacles	
	B 5133-0	PBT, Black Accepts 3-5 mm cable diameter Screw terminals, accepts up to 22 AWG conductors 85°C 60 VAC/ 75 VDC, 4 A	Mates with 3-pin threaded cordsets and receptacles	
	B 5143-0	PBT, Black Accepts 3-5 mm cable diameter Screw terminals, accepts up to 22 AWG conductors 85°C 60 VAC/ 75 VDC, 4 A	Mates with 4-pin threaded cordsets and receptacles	
	B 5231-0	PBT, Black Accepts 3-5 mm cable diameter Solder terminals, accepts up to 24 AWG conductors 85°C 60 VAC/ 75 VDC, 4 A	Mates with 3-pin threaded cordsets and receptacles	
	B 5241-0	PBT, Black Accepts 3-5 mm cable diameter Solder terminals, accepts up to 24 AWG conductors 85°C 30 VAC/ 36 VDC, 3.0 A	Mates with 4-pin threaded cordsets and receptacles	