




354 Series





ABSOLUTE MAXIMUM RATINGS (Ta = 25°C)

REVERSE VOLTAGE	_____	5V
REVERSE CURRENT (VR=5V)	_____	100µA
OPERATING TEMPERATURE RANGE	_____	-25°C ~ 85°C
STORAGE TEMPERATURE	_____	-30°C ~ 100°C
LEAD SOLDERING TEMPERATURE (1/16" FROM BODY)	_____	260°C for 5 Seconds



STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		MARL	MARL BUSINESS PARK, ULVERSTON, UK. LA12 9BN Tel: +44 (0)1229 582 430. Web: www.leds.co.uk
DECIMALS	ANGULAR		
.X ±.1	X° ± 1°		
.XX ±.02		TITLE: STD PANEL MOUNT INDICATORS	
.XXX ±.010		PART NO: 354 Series	
Provisional		SHEET # 1 OF 3	
		CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.	

354 Series (Flying Leads version)



STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		MARL	MARL BUSINESS PARK, ULVERSTON, UK. LA12 9BN Tel: +44 (0)1229 582 430. Web: www.leds.co.uk
<u>DECIMALS</u>	<u>ANGULAR</u>		
.X ± .1	X° ± 1°		
.XX ± .02		⊕ □	TITLE: STD PANEL MOUNT INDICATORS
.XXX ± .010			PART NO: 354 Series
Provisional		SHEET # 2 OF 3	
<small>CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.</small>			

Marl Part No.	Chip			Lens Appearance	Electro-Optical Data @20mA				Viewing Angle 2 Ø 1/2 (Deg)	LED P/N	Termination
	Material	Peak Wave Length	Emitted Colour		If (mA)	Vf (V)		Iv (mcd)			
						MAX	TYP				
354-320-04	GaN/SiC	430	BLUE	DIFFUSED	25	4	4.5	10	40	320	PINS
354-320-04-40											12IN FLYING LEADS
354-314-04	GaP/GaP	568	GREEN	DIFFUSED	30	2.1	2.8	25	40	314	PINS
354-314-04-40											12IN FLYING LEADS
354-305-04	GaP/GaP	700	RED	DIFFUSED	20	2.1	2.8	2	40	305	PINS
354-305-04-40											12IN FLYING LEADS
354-311-04	GaAsp/GaP	590	YELLOW	DIFFUSED	30	2	2.8	20	40	311	PINS
354-311-04-40											12IN FLYING LEADS

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)			MARL BUSINESS PARK, ULVERSTON, UK. LA12 9BN Tel: +44 (0)1229 582 430. Web: www.leds.co.uk
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°		TITLE: STD PANEL MOUNT INDICATORS
.XX ± .02			PART NO: 354 Series
.XXX ± .010			SHEET # 3 OF 3
Provisional		CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.	