



Line Reel Balancer
35.5 in./901 mm
LR-09B-90

- Designed for use with small pneumatic tools for light duty applications
- Integrating air hose and support cable keep work areas tidy
- Adjustable ball stop for optional positioning
- Polyvinyl hose 1/4" N.P.T. 1/4" inlet 700 mm
- 360 degree upper swivel
- Maximum 142 PSI



Specifications:

Model No:	LR-09B-90
Body Dia - in:	4.9
Body Dia - mm:	125
Body Width - in:	3.64
Body Width - mm:	92.5
Hose Length - in:	35.5
Hose Length - m:	0.9
Stroke - in:	27.56
Stroke - mm:	0.7
Weight - kg:	0.85
Weight - lbs:	1.87
Weight Capacity - kg:	1.36
Weight Capacity - lbs:	3