

Search for a Spring



[Home](#) | [Stock Springs](#) | [Custom Springs](#) | [Full Product Range](#) | [About Springmasters](#) | [Quality Assurance](#) | [Contact Us](#) | [Search for your part number](#) | [Privacy](#)

[Back to extension springs](#)

Extension Spring Database Results.

Find the web page holding all of the Part Number information.



Specifications & Materials

Music Wire to DIN 17223,
Class C. No.1.1200 or BS 1408 CR3.

Stainless Steel Wire to DIN 17224,
No.1.14310 or BS 2056 302S26.

Ends: German loops, random position

Note: All Springmasters Extension Springs are right hand coiled.

Tolerances: All dimensions and forces conform to DIN 2095 (Grade 2) or BS 1726 Class B.

Surface Finish:

Music Wire = Oiled
Stainless Steel = Self

Recommended Working Temps:

Music Wire = 120°C (max.)
Stainless Steel = 300°C (max.)

Wire dia mm	Outside dia mm	Free length mm	Rate N/mm	Code number
0.63	7	25.6	0.25	T31140
0.63	7	35	0.16	T31150
0.63	7	47.6	0.11	T31160
0.66	4.78	12.7	3.99	E7702310
0.66	4.78	15.88	2.34	E7702320
0.66	4.78	19.05	1.65	E7702330
0.66	4.78	22.23	1.28	E7702340
0.66	4.78	25.4	1.04	E7702350
0.66	4.78	28.58	0.88	E7702360
0.66	4.78	31.75	0.76	E7702370

[« Previous results](#) - Number of results: 1200 - [Next results »](#)

Note: Extension spring search results will include a +10% tolerance.

For your imperial sized extension spring requirements please [contact Springmasters](#) with your specifications.



Assorted Boxes of Extension (Tension) Springs

Buy online... [assorted imperial](#) and [assorted metric](#) extension springs.

[Extension Springs Homepage](#) | [Contact us about extension springs](#)

Springmasters Ltd
Registered in England & Wales No. 897155
Arthur Street, Lakeside
REDDITCH B98 8LF United Kingdom



T: +44 (0)1527 521000 | F: +44 (0)1527 528866 | E: sales@springmasters.com

Copyright ©2012 Springmasters Ltd - All rights reserved. Site Design by Web Design, Sheffield using Validated HTML & CSS
