

## SPECIFICATIONS

Metric						
Code No.	Range	Accuracy	Graduation	Depth bar	Remarks	Price
530-102	0 - 150 mm	±0.05 mm	0.05 mm	ø1.9 mm rod	—	£43.50
530-101				—	£29.90	
530-320				Carbide-tipped jaws for outside measurement	£94.50	
530-108	0 - 200 mm	±0.08 mm		Blade	—	£56.90
530-321					Carbide-tipped jaws for outside measurement	£96.40
530-109					—	£158.00
530-322	0 - 300 mm	Carbide-tipped jaws for outside measurement			£250.00	
530-501	0 - 600 mm				—	£388.00
530-502	0 - 1000 mm	±0.15 mm			—	£878.00


Inch/Metric						
Code No.	Range	Accuracy	Graduation	Depth bar	Remarks	Price
530-104	0 - 150 mm (0 - 6")	±0.05 mm	0.05 mm (1/128")	Blade	—	£39.60
530-312		±0.03 mm	0.02 mm (.001")		High accuracy model	£39.60
530-118	0 - 200 mm (0 - 8")	±0.03 mm	0.02 mm (.001")		High accuracy model: ±0.03 mm	£56.90
530-115	0 - 300 mm (0 - 12")	±0.08 mm	0.05 mm (1/128")		—	£158.00
530-119		±0.04 mm	0.02 mm (.001")		High accuracy model: ±0.04 mm	£158.00

### Measurement Applications

1. Outside measurement



2. Inside measurement



3. Step measurement



4. Depth measurement

