



## Stubby Combination Spanners



Size (mm)	Size (mm)
B-S1008	8.0
B-S1009	9.0
B-S1010	10.0
B-S1011	11.0
B-S1012	12.0
B-S1013	13.0
B-S1014	14.0
B-S1015	15.0



- CR-V
- 12pt flank profile
- 15° offset jaw
- DIN 3113/ANSI standard

## 8Pc Stubby Combination Spanner Set



**B-S0008**

Sizes (mm)	8.0   10.0   12.0   13.0   14.0   15.0   17.0   19.0
Supplied in	Clip pack



- CR-V
- 12pt flank profile
- 15° offset jaw
- DIN 3113/ANSI standard

## Combination Spanners



Size (mm)	SAE AF	Size (mm)	SAE AF	Size (mm)	SAE AF
MET1108	8.0	5/16"	MET1116	16.0	5/8"
MET1109	9.0	11/32"	MET1117	17.0	11/16"
MET1110	10.0	3/8"	MET1118	18.0	23/32"
MET1111	11.0	7/16"	MET1119	19.0	3/4"
MET1112	12.0	15/32"	MET1120	20.0/21.0	13/16"
MET1113	13.0	1/2"	MET1122	22.0/23.0	7/8"
MET1114	14.0	9/16"	MET1124	24.0	15/16"
MET1115	15.0	19/32"	MET1126	26.0/27.0	1 1/16"



- Patented Metrinch wall drive profile
- Operates on both metric and inch series fasteners
- Can be used on worn and damaged bolts
- Can be used on open-end spanners as well as on sockets and ring-spanners

## 6Pc/7Pc Combination Spanner Set



**MET0106**

**MET0107**

Sizes (mm)	10.0   11.0   13.0   14.0   16.0   17.0	As left plus 19.0
------------	---	-------------------

Supplied in Clip pack



## 10Pc Combination Spanner Set



**MET0110**

Sizes (mm)	10.0   11.0   12.0   13.0   14.0   15.0   16.0   17.0   18.0   19.0
------------	---

Supplied in Canvas wallet



CORDLESS POWER TOOLS

AIR TOOLS

HAND TOOLS

TOOL STORAGE

WORKSHOP EQUIPMENT

SPECIALIST VEHICLE TOOLS