



Masking Tape 203



***Construction strength
for cost-effective bundling,
attaching, holding, and more***

3M™ Masking Tape 203 is the cost-effective choice for bundling, holding, attaching, sealing, wrapping, and masking.

- New construction strength for high holding power, the convenience of tearing by hand, and the strength for reliable bundling
- Easy, controlled unwind from the roll
- Instant adhesion to a wide variety of surfaces with high holding power that resists lifting and curling
- Crepe backing conforms and seals around corners
- Removes cleanly from most substrates for up to 24 hours
- Temperature resistance of up to 200°F (93°C) for up to 30 minutes
- Can be qualified to meet CID-A-A-883 Type I specification

3M.com/masking



*From hanging poly drapes to attaching production notes
and instructions*





3M™ Masking Tape 203

Unwinds easily,
conforms, and
tears by hand



*Tight seal around
curves and corners*

5



6

Product	UPC #	Size*	Total Thickness mils (mm) (N/100 mm)	Adhesion oz./in. width (N/100 mm)	Tensile Strength lbs./in. width	Elongation at Break %	Rolls/ Case
203 Bulk	58068-5	12 mm	5.2 (0.13)	35 (37)	20 (350)	9	72
	58035-8	18 mm	5.2 (0.13)	35 (37)	20 (350)	9	48
	58036-4	24 mm	5.2 (0.13)	35 (37)	20 (350)	9	36
	58037-1	36 mm	5.2 (0.13)	35 (37)	20 (350)	9	24
	58038-8	48 mm	5.2 (0.13)	35 (37)	20 (350)	9	24
	58039-5	72 mm	5.2 (0.13)	35 (37)	20 (350)	9	12
	58040-1	96 mm	5.2 (0.13)	35 (37)	20 (350)	9	8
203 Individual Wrap	58499-7	18 mm	5.2 (0.13)	35 (37)	20 (350)	9	48
	58452-2	24 mm	5.2 (0.13)	35 (37)	20 (350)	9	36
	58453-9	36 mm	5.2 (0.13)	35 (37)	20 (350)	9	24
	58454-6	48 mm	5.2 (0.13)	35 (37)	20 (350)	9	24

*All rolls are 55 m long

A. PRODUCT USE: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

B. WARRANTY AND LIMITED REMEDY: Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

C. LIMITATION OF LIABILITY: Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



**Industrial Business
Industrial Adhesives and Tapes Division**

Building 21-1W-10
900 Bush Avenue
St. Paul, MN 55144-1000
1 800 362 3550
www.3M.com/masking