

KNIPEX 8" Electrical Installation Pliers



The mobile task force – for cutting, stripping, crimping, gripping, bending and deburring.

KNIPEX has designed a new type of installation pliers to complement your diagonal cutter. These pliers combine the basic functions of 5 other tools, which are essential for electrical installation; Side Cutting Pliers, Long Nose Pliers, Wire Strippers, Crimping Pliers and Cable Shears. This multifunctional pair of pliers is ideal for electricians who want to reduce the amount of tools they carry.

- 6 functions in one pair of pliers
 - **Cutting:** cable shears with induction hardened cutting edges for copper and aluminum cables; cuts stranded wire up to 9/16" and solid wire up to 5/32"
 - **Stripping:** stripping holes for 12 and 14 AWG
 - **Crimping:** crimp die for 12-20 AWG
 - **Gripping:** serrated gripping surfaces and pipe grip for flat and round material
 - **Bending:** smooth surface near the tips for a non-damaging grip when forming wire loops
 - **Deburring:** clear-cut outside edge for reaming conduit or pipe and for deburring feed-through holes
- slim long nose design for easy access into tight places
- bolted joint for precision smooth action
- forged from German high-grade special tool steel



Product Number	Description	Carded Packaging	Handles	Stripping Capacity (AWG)	Cutting Capacity Stranded	Cutting Capacity Solid	Crimping
13 81 8	8" Electrical Installation Pliers	n	plastic dipped	12 and 14	9/16"	5/32"	12-20
13 81 8 SBA	8" Electrical Installation Pliers	y	plastic dipped	12 and 14	9/16"	5/32"	12-20
13 82 8	8" Electrical Installation Pliers	n	multi-component grips	12 and 14	9/16"	5/32"	12-20
13 82 8 SBA	8" Electrical Installation Pliers	y	multi-component grips	12 and 14	9/16"	5/32"	12-20
13 88 8 US	8" Electrical Installation Pliers, Insulated	n	1000V insulated	12 and 14	9/16"	5/32"	12-20
13 88 8 SBA	8" Electrical Installation Pliers, Insulated	y	1000V insulated	12 and 14	9/16"	5/32"	12-20



2035 S. Arlington Heights Rd., Suite 110, Arlington Heights, IL 60005 | 847.398.8520 • 847.398.8526 (fax) | www.knipex-tools.com

KNIPEX Quality – Made in Germany