

Semi-Flexible Rules

SERIES 182

FEATURES

- Engraved on frontside only



182-304

SPECIFICATIONS

Inch/Metric

Order No.	Size	Graduations	Width	Accuracy (Length)
182-301	4" x 100mm	1/2mm 1mm 1/32 1/64 1/16th	5/8"	+0.004" / -0.0035"
182-302	6" x 150mm	1/2mm 1mm 1/32 1/64 1/16th	5/8"	(+0.1mm / -0.09mm)
182-303	8" x 200mm	1/2mm 1mm 1/32 1/64 1/16th	5/8"	+0.005" / -0.0035"
182-304	10" x 250mm	1/2mm 1mm 1/32 1/64 1/16th	5/8"	+0.13mm / -0.09mm)
182-305	12" x 300mm	1/2mm 1mm 1/32 1/64 1/16th	5/8"	
182-307	20" x 500mm	1/2mm 1mm 1/32 1/64 1/16th	5/8"	+0.007" / -0.0035" (+0.18mm / -0.09mm)
182-309	40" x 1000mm	1/2mm 1mm 1/32 1/64 1/16th	5/8"	+0.008" / -0.004" (+0.2mm / -0.1mm)

Hook Rules

SERIES 182

FEATURES

- Hardened and tempered tool steel.
- Hard chrome finish.
- Furnished with adjustable hook.



182-421

SPECIFICATIONS

Order No.	Size	Graduations	Width	Accuracy (Length)
182-421	6" (4R)	1/8 1/16 1/32 1/64	3/4"	+0.004" / -0.0035"
182-422	12" (4R)	1/8 1/16 1/32 1/64	1"	+0.005" / -0.0035"
182-423	18" (4R)	1/8 1/16 1/32 1/64	1-1/8"	+0.006" / -0.0035"
182-424	24" (4R)	1/8 1/16 1/32 1/64	1-1/8"	+0.007" / -0.0035"

Pocket Steel Rule

SERIES 950

FEATURES

- Engraved on frontside only.
- Backside: Inch/Metric equivalents



950-300

SPECIFICATIONS

Order No.	Size	Graduation	Width	Accuracy (Length)
950-300	6" x 150mm	1mm	1/2"	+0.004" / -0.0035" (+0.1mm / -0.09mm)
950-301	6"	1/32nds	1/2"	+0.004" / -0.0035"