

New! GLM 30 Professional Laser Measurer

New! GLM 30 Professional Laser Measurer

The one button,
compact solution for
measuring distances



| Part Number | Description | Best Nett | RRP (ex VAT) |
|---------------|----------------------------|-----------|--------------|
| 0.601.072.570 | New! GLM 30 Laser Measurer | £50.82 | £66.00 |



BOSCH

1. GLM 30 Professional – Overview and key messages

1. One button operation for quick ease of use.
2. Good working range for all general construction sites of up to 30 metres.
3. Automatically illuminated display for clear visibility of results.
4. Unique auto-sum feature to help with material calculations.
5. Compact design so it easily fits in a pocket.






2. GLM 30 Professional – Features and benefits

Automatically illuminated display

Range and accuracy ISO certified



IP54 protection



Auto sum feature for material calculations

One button for easy operation

Hold button down whilst device is switched off to change between **metric and imperial** units

Soft grip for protection on all sides



BOSCH

3. GLM 30 Professional – Applications and target users

Target Groups

- Electricians
- Dry-wall construction workers
- Painting and maintenance
- General construction workers
- Carpenters/cabinet makers





Main application

- Basic length measurements
- Calculating material needs for electrical installations
- Estimate material costs on site
- All other measuring applications



4. GLM 30 Professional – Competitor analysis

| | Bosch GLM 30  | Hilti PD 5  |
|--------------------------|---------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|
| Technical Data | | |
| Working Range | 0,15-30 m | 0,05 - 70 m |
| Typ. Accuracy (laser) | ± 2mm | ± 1,5 mm |
| ISO certified | ✓ | ✗ |
| IP class | 54 | 55 |
| Number of buttons | 1 | 2 |
| Tripod Mount (1/4") | ✗ | ✗ |
| Display illumination | ✓ | ✓ |
| Size | 105 x 41 x 24 mm | 164 x 33 x 21 mm |
| Weight | 0,1 kg | 0,1 kg |
| Functionality | | |
| Rear reference | ✓ | ✓ |
| Front reference | ✗ | ✗ |
| Length Measurement | ✓ | ✓ |
| Area Measurement | ✗ | ✗ |
| Volume Measurement | ✗ | ✗ |
| Continuous Measurement | ✗ | ✓ |
| Auto-sum feature | ✓ | ✗ |
| Min/max Measurement | ✗ | ✗ |
| Calculation (+/-) | ✗ | ✗ |
| Memories | ✗ | ✗ |
| Indirect Measurements | ✗ | ✗ |
| POM GBP | £66 | £105* |
| Scope of delivery | | |
| | 2 x AAA batteries | 2 x AAA batteries, protective pouch, belt clip |

*average POM price from UK internet prices



BOSCH

5.1 GLM 30 Professional – Specifications

| Specification | GLM 30 Professional |
|---------------------------------------|-----------------------|
| Laser class & type | Class 2, 635 nm, <1mW |
| Laser measuring range | 0.15 – 30 m |
| Measuring accuracy | +/- 2 mm |
| Battery type | 2 x 1.5 V LR03 (AAA) |
| Maximum number of single measurements | 5,000 |
| Drop test resistance | 1 m |
| Dust and water splash protection | IP54 |
| Dimensions | 105 x 41 x 24 mm |
| Weight | 0.1 kg |



BOSCH

5.2 GLM 30 Professional – Scope of delivery

| Part number Short code | Description |
|---------------------------|---------------------------------------------------------------------------------------------------------------|
| 0601072570 GLM30 | <ul style="list-style-type: none">• Bare tool• 2 x AAA batteries• User manual |

