

## Coupler connector - ST-08S1N8A9K04S - 1618726


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Coupler connector, straight, SPEEDCON locking, M17, Number of positions: 8, Type of contact: Socket, Crimp connection, shielded: Yes, Cable diameter: 9 mm...11 mm



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 811972
Weight per Piece (excluding packing)	44.44 g
Custom tariff number	85366990
Country of origin	Germany
Product key	ABRBEI
Note	Made to Order (non-returnable)

### Technical data

#### General

Type of locking	SPEEDCON locking
Direction of rotation of contact chamber numbering	Standard
Coding	N
Contact connection method	Crimp connection
Type of contacts	Socket
Number of positions	8
Contact diameter of power contacts	1 mm
Nominal current per power contact at 25°C	3.6 A
Conductor entry	9 mm ... 11 mm

#### Ambient conditions

Degree of protection	IP67
----------------------	------

#### Specifications according to DIN EN 61984:2001

Installation height max.	3000 m
Nominal / operating voltage of power contacts	60 V

# Coupler connector - ST-08S1N8A9K04S - 1618726

## Technical data

Specifications according to DIN EN 61984:2001

Rated surge voltage of power contacts	1.5 kV
Surge voltage category of power contacts	II
Pollution degree of power contacts	3

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260702
eCl@ss 7.0	27440102
eCl@ss 8.0	27440102

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002635
ETIM 5.0	EC002635

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

## Approvals

### Approvals

---

Approvals

cUL Recognized / cUL Recognized

---

Ex Approvals

---


Approvals submitted


---

### Approval details

# Coupler connector - ST-08S1N8A9K04S - 1618726

## Approvals

cUL Recognized 	
Nominal current I <sub>N</sub>	1 A
Nominal voltage U <sub>N</sub>	60 V

cUL Recognized 	
--	--

## Drawings

Schematic diagram



Connector pin assignment

Dimensioned drawing

