



Quam

ATTENUATORS

QC100

2-GANG

**UL LISTED, 100W, 10-Step,
Stainless Steel Faceplate, Embossed Positions**

GENERAL DESCRIPTION


The **QC100** is a UL Listed, 2-gang, 100W, ten-step, continuous rotary, audio level attenuator with an OFF position. Brushed, stainless steel faceplate with embossed positions and a black knob with white indicator mark.

INTENDED USE - Indoor Environment

Primary Use	Attenuates audio power to any number of loudspeakers, up to 100W load. For use with 25V or 70V distributed audio systems.
UL LISTED 813 Commercial Audio Equipment	When installed in accordance with supplied instructions and connected to supply circuits in accordance with ANSI/NFPA70, NEC, and AHJ.
Installation	2-gang electrical box, 2-1/8"D

AUDIO SPECIFICATIONS

Power Rating	100W Continuous
Attenuation	Position 10 : Full Signal
(Ref: 25V, 70.7V line)	Position 9-3 : -3 dB each
	Positions 2-1 : -6 dB each
	Position 0 : No Signal
Insertion Loss	<0.5 dB
Audio Connection	10" long, pre-cut, color coded leads



Recommended construction sequences, installation instructions, and A&E Specifications are available in various formats in the QUAM Architects' and Engineers' Resources section on the web at:
www.QuamSpeakers.com

© 2013 Quam-Nichols Company reserves the right to make changes and/or improvements to its products at any time and without notice.



QUAM-NICHOLS COMPANY, INC.
234 East Marquette Rd.
Chicago, IL. 60637
Tel: 1-800-NEED-NOW (800-633-3669)
Fax: 1-888-NEED-NOW (888-633-3669)
e-mail: NeedNow@QNC.com
www.QuamSpeakers.com