

ZyXEL NSA325 v2 (NSA325V2-EU0101F)

ZyXEL NSA325 2-Bay Power Plus NAS Appliance Diskless - 1.6GHz CPU, up to 4TB capacity, JBOD, RAID 0, 1, Gigabit LAN port, 1xUSB3.0, 2xUSB2.0, DLNA 1.5, SATA/SATA II, Wake-on-LAN, Full License Memeo Backup included.



The ZyXEL media server is more than just a central home media library. You can effortlessly share and upload media stored on the NSA325 v2 through mobile devices. Using the Polkast app on your mobile devices, you can access all the photos, music and videos stored on the NSA325 v2 and share them with friends or family. You can synchronize photos on Facebook, Twitter or Flickr to your NSA325 v2 through Polkast; stream music to play-zone and control them with a remote or mobile device wherever you go.

## Key Selling Points

Superior performance with powerful 1.6 GHz processor

Access your personal cloud from any mobile devices with Polkast app

Easy configuration through tablets and mobile devices

USB 3.0 port provides faster backup from USB devices

All-in-one backup solution for protection of valuable user data

Energy-efficient design with Wake-on-LAN, power scheduling and hard disk hibernation functions

## Main Specifications

Product Description	ZyXEL NSA325 v2 - NAS server
Device Type	NAS server
Host Connectivity	Gigabit Ethernet
Installed Devices / Modules Qty	0 (installed) / 2 (max)
Dimensions (WxDxH)	20.7 cm x 16.4 cm x 12.3 cm
Weight	1.257 kg
Localisation	Europe
Processor	1 x 1.6 GHz
Storage Controller	RAID - SATA 6Gb/s - RAID 0,1,JBOD
Networking	Network adapter 10Mb LAN,100Mb LAN,GigE
Power	AC 120/230 V ( 50/60 Hz )
System Requirements	Microsoft Windows Vista (32/64 bits),Microsoft Windows 7 (32/64 bits),Microsoft Windows XP (32/64 bits),Windows 8 (32/64 bits)
Manufacturer Warranty	2 years warranty

## Extended Specification

### General

Device Type	NAS server
Host Connectivity	Gigabit Ethernet
Installed Devices / Modules Qty	0 (installed) / 2 (max)
Width	20.7 cm
Depth	16.4 cm
Height	12.3 cm
Weight	1.257 kg
Localisation	Europe

### Processor / Memory

Processors Installed	1 x 1.6 GHz
----------------------	-------------

### Storage Controller

Type	RAID
Interface Type	SATA 6Gb/s
RAID Level	RAID 0,RAID 1,JBOD

#### Hard Drive

Type	HDD
------	-----

#### Networking

Type	Network adapter
------	-----------------

Data Link Protocol	10Mb LAN,100Mb LAN,GigE
--------------------	-------------------------

Network / Transport Protocol	NTP,PPPoE,DHCP
------------------------------	----------------

Network Services Compatibility	Microsoft CIFS,Network File System (NFS),FTP,Server Message Block (SMB),HTTP
--------------------------------	--

Features	Wake on LAN (WOL),MySQL server,web server,backup server,P2P client,iTunes server,FTP server,temperature sensor,UPnP Media Server,reset button,DLNA Media Server,Apple Time Machine compatible,Receive Side Scaling (RSS),DHCP client
----------	--

Encryption Algorithm	SSL,TLS
----------------------	---------

Compliant Standards	DLNA CERTIFIED,UPnP
---------------------	---------------------

#### Expansion / Connectivity

Expansion Bays	2 (total) / 2 (free) x internal - 2.5" / 3.5"
----------------	---

Interfaces	1 x Ethernet 1000Base-T - RJ-45 2 x USB 2.0 - Type A 1 x USB 3.0 - Type A
------------	---

#### Miscellaneous

Cables Included	1 x network cable
-----------------	-------------------

Features	Security lock slot (cable lock sold separately),cable organizer,UPS support
----------	---

Compliant Standards	FCC Class B certified,C-Tick,BSMI,LVD
---------------------	---------------------------------------

#### Power

Power Device	X external power adapter
--------------	--------------------------

Voltage Required	AC 120/230 V ( 50/60 Hz )
------------------	---------------------------

Power Consumption Operational	27 Watt
-------------------------------	---------

#### Software / System Requirements

Software Included	Drivers & Utilities
-------------------	---------------------

OS Required	Microsoft Windows Vista (32/64 bits),Microsoft Windows 7 (32/64 bits),Microsoft Windows XP (32/64 bits),Windows 8 (32/64 bits)
-------------	--

#### Manufacturer Warranty

Service & Support	2 years warranty
-------------------	------------------

Service & Support Details	Limited warranty - 2 years
---------------------------	----------------------------

#### Environmental Parameters

Min Operating Temperature	0 °C
---------------------------	------

Max Operating Temperature	40 °C
---------------------------	-------

Humidity Range Operating	10 - 95% (non-condensing)
--------------------------	---------------------------

Product data is provided by CNET, we do not warrant the accuracy and completeness of the material contained in this data sheet