

Omnimate Range - 5.08 mm Pitch

Pin headers SL 5.08/180B



Technical data VDE UL CSA

Rated voltage (V) 250* 300 300

Rated current (A) 12 15 15

*Pollution severity 3 / Overvoltage category III

Solder pin length 4.5 mm 4.5 mm
Color Orange Black

Poles	Type	Part No.	Part No.	Qty.
2	SL 5.08/2/180B	1524160000	1524110000	100
3	SL 5.08/3/180B	1524260000	1524210000	100
4	SL 5.08/4/180B	1524360000	1524310000	100
5	SL 5.08/5/180B	1524460000	1524410000	50
6	SL 5.08/6/180B	1524560000	1524510000	50
7	SL 5.08/7/180B	1524660000	1524610000	50
8	SL 5.08/8/180B	1524760000	1524710000	50
9	SL 5.08/9/180B	1524860000	1524810000	50
10	SL 5.08/10/180B	1524960000	1524910000	50
11	SL 5.08/11/180B	1525060000	1525010000	50
12	SL 5.08/12/180B	1525160000	1525110000	50
13	SL 5.08/13/180B	1525260000	1525210000	50
14	SL 5.08/14/180B	1525360000	1525310000	50
15	SL 5.08/15/180B	1525460000	1525410000	50
16	SL 5.08/16/180B	1525560000	1525510000	50
17	SL 5.08/17/180B	1525660000	1525610000	20
18	SL 5.08/18/180B	1525760000	1525710000	20
19	SL 5.08/19/180B	1525860000	1525810000	20
20	SL 5.08/20/180B	1525960000	1525910000	20
21	SL 5.08/21/180B	1526060000	1526010000	20
22	SL 5.08/22/180B	1526160000	1526110000	20
23	SL 5.08/23/180B	1526260000	1526210000	20
24	SL 5.08/24/180B	1526360000	1526310000	20