This document was generated on 10/15/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: 51015-1400

Status: Active

Description: 2.00mm Pitch Board-in Crimp Housing, Low Profile, 14 Circuits

Documents:

3D Model
Drawing (PDF)
Product Specification PS-51015-001 (PDF)
Product Specification PS-51015-002 (PDF)
RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family	Crimp Housings
Series	51015
Application	Signal
Product Name	Board-In
UPC	800753575820

Physical

Circuits (maximum)	14
Color - Resin	Natural
Gender	Male
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	260.600/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Material Info

Reference - Drawing Numbers

Product Specification	PS-51015-001, PS-51015-002, RPS-51015-001, RPS-51015-003, RPS-51015-004, RPS-51015-006
Sales Drawing	SD-51015-**00

EU RoHS
ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the Contact Us section for any non-product compliance questions.

Search Parts in this Series
51015Series

Use With
50034

This document was generated on 10/15/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION