



• Black Box Products

Datacom > Converters

[click photo to enlarge](#)

Async RS-232 to RS-422 Interface Bidirectional Converter, DB9 Female to RJ-45



Enables your high-speed RS-232 devices to communicate with your RS-422 devices.

IC631A-F

Extended Double Diamond™ Warranty Available

(3 Additional Year)

Product Highlights

- Full-duplex data transmission over four wires.
- Distances up to 4000 feet (1219.2 m).
- Async data rates up to 19.2 kbps.



- [Details](#)
- [Tech Specs](#)
- [Resources](#)
- [Accessories](#)
- [Warranty](#)

Description

Async RS-232 to RS-422 Interface Bidirectional Converter, DB9 Female to RJ-45

Quick Facts

- Full-duplex data transmission over four wires.
- Distances up to 4000 feet (1219.2 m).
- Async data rates up to 19.2 kbps.

Further Details

- The RS-232 connector is DB9 female; the RS-422 connector is RJ-45.
- Connects directly to RS-232 equipment.
- No power supply required—power is drawn from RS-232 data and control signals.