


ROHS Compliant

Code:AADSL



SPECIFICATION

Right angled BT plug, BT (phone)+RJ11(DSL) sockets

MATERIAL

PLASTIC HOUSING:ABS
PLUG & SOCKET CONTACTS:PHOSPHOR BRONZE,
GOLD PLATED OVER NICKEL


ELECTRICAL

GENERAL REQUIREMENT:
SEE ELECTRICAL REQUIREMENT SHEET PA-P678
CONTACT RESISTANCE 35mOHMS MAX.
INSULATION RESISTANCE: 20 MEG OHMS MIN AT 100V DC.

WITHSTAND HARSH ENVIRONMENT

ALL CONTACTS COATED WITH PROTECTION LIQUID
SA-528 TO WHITHSTAND HUMIDITY.
PLUG & SOCKET MATING CYCLE UP TO 1000 TIMES.
WORKING TEMPERATURE: -20° C~60° C.
WORKING HUMIDITY: 0%~90%RH.

WIRING:



NO	Name	Material	Specification	Qty	Remark
6.	Wire	PVC	26 AWG(7X0.16) UL1061	4	BLACK;RED;GREEN;YELLOW
5.	BT JACK	PBT	6P4C 6U" GOLD WH(BN:J1)	1	
4.	SPLITTER	Capacitor	MEF	393J/400V	1
		Transformer	—	4.5mH	1
		PCB	FR-4	60.8x20.8x1.0mm	1
3.	RJ11 JACK	PBT	6P4C 6U" GOLD WH	1	
2.	UK PLUG	PC	6P4C 6U" GOLD WH	1	
1.	HOUSING	ABS	WH	2	