



Thermo-Shrink® Thin-Wall Heat Shrinkable Tubing Disks



Features

- Space-saving, no-waste dispenser holds up to 4 ft. of tubing
- TS-46 irradiated cross-linked polyolefin with 2:1 standard shrink ratio
- Shrink temperature of 120°C
- Forms tough, smooth insulated covering resistant to fluids and solvents

Models & Specifications

Tubing Size (Inches)	Expanded Inside Diameter (Minimum)	Recovered Inside Diameter (Maximum)	Wire Size*	Nominal Recovered Wall Thickness	Cat. No.
3/64	.046	.023	22-18 AWG	.018	46-600
1/16	.063	.031	16 AWG	.018	46-601
3/32	.093	.046	14-12 AWG	.020	46-602
1/8	.125	.062	24-20 AWG	.020	46-603
3/16	.187	.093	20-14 AWG	.020	46-604
1/4	.250	.125	14-8 AWG	.025	46-605
5/16	.312	.156	4-1 AWG	.025	46-606
3/8	.375	.187	8-4 AWG	.025	46-607
1/2	.500	.250	4-1 AWG	.025	46-608
3/4	.750	.375	2-250 AWG	.030	46-609
1	1.00	.500	2/0-500 MCM	.035	46-610

* Consult the wire manufacturer's catalog for specific O.D. of wire and insulation