



Plain Edge Cable Clamps

T&B Catalog Number: N6NY-012-0-C  
UPC Number: 72849409150  
Status: Active

Description:  
Cable Clamp Plain Edge Black Nylon 6/6 #10 Screw Mounting with Closed Diameter 0.750

- Features
- Fully radiused inside edges with size markings in inches and millimeters for easy identification.
  - Plain edge cable clamps are designed to perform to NAS-1397P.

General	
Material	Nylon 6/6
Color	Black
Mounting Method	#10 Screw
Dimension Information	
Width (inches)	0.500
Hole Diameter (inches)	0.203
Closed Diameter (inches)	0.750
Max. Wire Bundle Diameter (inches)	0.750
Thickness (inches)	0.060
E (inches)	0.699
X (inches)	0.218
Specifications	
Temperature Rating	-40°F to 185°F
Packaging	
Order Multiple	100
Inner Package	100
Outer Package	5000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.44 lbs. per 100
Certifications	
RoHS Compliance	Yes